

ZU 1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The strain relief protects the contact against mechanical stress and protects the connector against inadvertent release from the contact point.

General ordering data

| | |
|------------|----------------------------|
| Version | Accessories, Strain relief |
| Order No. | 0240600000 |
| Type | ZU 1 |
| GTIN (EAN) | 4008 1900 14940 |
| Qty. | 2 Stück |

ZU 1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Depth | 28 mm | Depth (inches) | 1.102 inch |
| Height | 102 mm | Height (inches) | 4.016 inch |
| Width | 90 mm | Width (inches) | 3.543 inch |
| Net weight | 75.425 g | | |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 100 °C |
|----------------------------------|--------|----------------------------------|--------|

Material data

| | | | |
|---------------------------|--------------|--------|-------|
| Material | Polyamide 66 | Colour | beige |
| UL 94 flammability rating | V-2 | | |

System specifications

| | |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

Additional technical data

| | | | |
|---------------------|-----------------|----------------|-----------------|
| Installation advice | Direct mounting | Type of fixing | when screwed in |
| Type of mounting | Plugged | | |

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002939 | ETIM 7.0 | EC002939 |
| ETIM 8.0 | EC002939 | ECLASS 9.0 | 27-40-08-45 |
| ECLASS 9.1 | 27-06-92-90 | ECLASS 10.0 | 27-40-08-45 |
| ECLASS 11.0 | 27-40-08-45 | ECLASS 12.0 | 27-40-08-45 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Engineering Data | WSCAD, EPLAN |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |