

EW 35/SCHA/M3**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Product image

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

| | |
|------------|----------------------------|
| Version | Accessories, End bracket |
| Order No. | 0258660000 |
| Type | EW 35/SCHA/M3 |
| GTIN (EAN) | 4008190033477 |
| Qty. | 20 pc(s). |

EW 35/SCHA/M3

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 32.5 mm | Depth (inches) | 1.28 inch |
| Height | 46 mm | Height (inches) | 1.811 inch |
| Width | 16.5 mm | Width (inches) | 0.65 inch |
| Net weight | 9.78 g | | |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 100 °C |
|----------------------------------|--------|----------------------------------|--------|

Material data

| | | | |
|---------------------------|-------|--------|-------|
| Material | Wemid | Colour | beige |
| UL 94 flammability rating | V-2 | | |

System specifications

| | | | |
|---------|-------------------|------|-------|
| Version | For the terminals | Rail | TS 35 |
|---------|-------------------|------|-------|

Additional technical data

| | | | |
|---------------------|-----------------|-----------|------------------|
| Installation advice | Direct mounting | Interlock | for screw fixing |
| Type of mounting | when screwed in | | |

Dimensions

| | |
|--------------|---------|
| TS 35 offset | 22.5 mm |
|--------------|---------|

General

| | | | |
|---------------------|-----------------|------|-------|
| Installation advice | Direct mounting | Rail | TS 35 |
|---------------------|-----------------|------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001041 | ETIM 7.0 | EC001041 |
| ETIM 8.0 | EC001041 | ECLASS 9.0 | 27-14-11-35 |
| ECLASS 9.1 | 27-14-11-35 | ECLASS 10.0 | 27-14-11-35 |
| ECLASS 11.0 | 27-14-11-35 | ECLASS 12.0 | 27-14-11-35 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | ffc2e92d-f68c-4edd-8818-3ff53f901c61 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

Creation date March 6, 2023 12:51:14 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.