


H50,0/36 OLIV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

| | |
|------------|---|
| Version | Wire-end ferrule, Standard, 26 mm, 20 mm, Olive green |
| Order No. | 0444200000 |
| Type | H50,0/36 OLIV |
| GTIN (EAN) | 4008 1901 10284 |
| Qty. | 50 pc(s). |
| Packaging | loose |

Creation date February 28, 2023 9:18:35 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

H50,0/36 OLIV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 2.8 g

Technical data

| Description of article | Wire end ferrule with plastic collar, olive green | Version | Standard |
|------------------------|---|---------|----------|
|------------------------|---|---------|----------|

Wire-end ferrules

| | | | |
|-----------------------------|--------------------|---|------------|
| Collar diameter (D2) | 15 mm | Colour code | Weidmüller |
| Conductor cross-section | 50 mm ² | Contact surface diameter (D1) | 10.3 mm |
| Contact surface length (L2) | 20 mm | L1 in mm | 36 mm |
| Metal sleeve thickness (S1) | 0.3 mm | Plastic collar thickness (S2) | 0.5 mm |
| Stripping length | 26 mm | Wire connection cross section AWG, max. | AWG 1 |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000005 | ETIM 7.0 | EC000005 |
| ETIM 8.0 | EC000005 | ECLASS 9.0 | 27-40-02-01 |
| ECLASS 9.1 | 27-40-02-01 | ECLASS 10.0 | 27-40-02-01 |
| ECLASS 11.0 | 27-40-02-01 | ECLASS 12.0 | 27-40-02-01 |

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E499744 |

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

Data sheet

H50,0/36 OLIV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

