

BS 25 IH/SW SAKT1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Fixing screws fix the short current bridge within the application. If the short current bridge is slided between two adjacent terminal blocks into the short circuit position, it can be fixed by means of a fastening screw. This ensures a permanent connection or short circuit.

General ordering data

| | |
|------------|----------------------------|
| Version | SAK Series, Set of fixings |
| Order No. | 0335200000 |
| Type | BS 25 IH/SW SAKT1 |
| GTIN (EAN) | 4008190114039 |
| Qty. | 50 pc(s). |

Creation date March 1, 2023 2:02:43 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

BS 25 IH/SW SAKT1

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|----------|---------|-----------------|------------|
| Depth | 28.7 mm | Depth (inches) | 1.13 inch |
| Height | 5.5 mm | Height (inches) | 0.217 inch |
| Width | 5.5 mm | Width (inches) | 0.217 inch |
| Diameter | 3 mm | Net weight | 1.74 g |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Material data

| | | | |
|----------|--------------|--------|-------|
| Material | Steel, Brass | Colour | black |
|----------|--------------|--------|-------|

System specifications

| | |
|---------|---------------------------|
| Version | for cross-connection link |
|---------|---------------------------|

Additional technical data

| | | | |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | No | Installation advice | Direct mounting |
| Type of fixing | when screwed in | Type of mounting | when screwed in |

Dimensions

| | |
|----------|------|
| Diameter | 3 mm |
|----------|------|

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002848 | ETIM 7.0 | EC002848 |
| ETIM 8.0 | EC002848 | ECLASS 9.0 | 27-14-11-92 |
| ECLASS 9.1 | 27-14-11-92 | ECLASS 10.0 | 27-14-11-92 |
| ECLASS 11.0 | 27-14-11-92 | ECLASS 12.0 | 27-14-11-92 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | cabfa93a-285a-4cc9-a7cb-2fefa00bc7a4 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

Creation date March 1, 2023 2:02:43 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.