


**QB 4 WI RA8 IS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	SAK Series, Cross-connector, Cross-connector, Number of poles: 4
Order No.	<a href="#">0461300000</a>
Type	QB 4 WI RA8 IS
GTIN (EAN)	4008 190025373
Qty.	50 pc(s).

Creation date February 28, 2023 5:23:08 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## QB 4 WI RA8 IS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	19 mm	Depth (inches)	0.748 inch
Height	28 mm	Height (inches)	1.102 inch
Width	3 mm	Width (inches)	0.118 inch
Net weight	1.73 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

### Material data

Material	PA 66	Colour	grey
UL 94 flammability rating	V-2		

### System specifications

Version	Cross-connector
---------	-----------------

### Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in	Type of mounting	when screwed in

### Cross-connector

Number of cross-connected terminals	4	Rated current, 2-pole	27 A
Rated current, multi-pole	27 A	Type	Cross-connector

### Dimensions

Pitch in mm (P)	8 mm
-----------------	------

### General

Installation advice	Direct mounting	Number of poles	4
---------------------	-----------------	-----------------	---

### Rating data

Rated current	27 A
---------------	------

### Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

**QB 4 WI RA8 IS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Approvals**

Approvals



ROHS

Conform

**Downloads**

Approval/Certificate/Document of  
Conformity

[EAC certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[WSCAD](#)

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)