

**QL 2 SAK10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	SAK Series, Cross-connector, for cross-connection link, Number of poles: 2
Order No.	<a href="#">0470300000</a>
Type	QL 2 SAK10
GTIN (EAN)	4008 190023690
Qty.	100 pc(s).

Creation date March 1, 2023 10:47:25 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## QL 2 SAK10

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	2 mm	Depth (inches)	0.079 inch
Height	6 mm	Height (inches)	0.236 inch
Width	16.9 mm	Width (inches)	0.665 inch
Net weight	1.35 g		

### Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

### Material data

Material	Cu Zn	Colour	grey
----------	-------	--------	------

### System specifications

Version	for cross-connection link
---------	---------------------------

### Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

### Cross-connector

Number of cross-connected terminals	2	Rated current, 2-pole	57 A
Rated current, multi-pole	57 A	Type	Cross-connector

### Dimensions

Pitch in mm (P)	9.9 mm
-----------------	--------

### General

Installation advice	Direct mounting	Number of poles	2
---------------------	-----------------	-----------------	---

### Rating data

Rated current	57 A
---------------	------

### Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

### Approvals

ROHS	Conform
------	---------

**QL 2 SAK10**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

---

Engineering Data	<a href="#">WSCAD</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

---