

**Q 2 SAK16****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	SAK Series, Cross-connector, for cross-connection link, Number of poles: 2
Order No.	<a href="#">0457500000</a>
Type	Q 2 SAK16
GTIN (EAN)	4008190055349
Qty.	50 pc(s).

**Q 2 SAK16**

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	20.5 mm	Depth (inches)	0.807 inch
Height	6 mm	Height (inches)	0.236 inch
Width	17.9 mm	Width (inches)	0.705 inch
Net weight	5.48 g		

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Material data**

Material	CuSn	Colour	grey
----------	------	--------	------

**System specifications**

Version	for cross-connection link
---------	---------------------------

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

**Cross-connector**

Number of cross-connected terminals	2	Rated current, 2-pole	76 A
Rated current, multi-pole	76 A	Type	Cross-connector

**Dimensions**

Pitch in mm (P)	6 mm
-----------------	------

**General**

Installation advice	Direct mounting	Number of poles	2
---------------------	-----------------	-----------------	---

**Rating data**

Rated current	76 A
---------------	------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

**Approvals**

Approvals



ROHS	Conform
------	---------

Creation date March 6, 2023 1:10:50 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

**Q 2 SAK16****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Downloads**Approval/Certificate/Document of  
Conformity[EAC certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[WSCAD](#)

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)