

## IE-FCM-USB-A

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Service interface FrontCom<sup>®</sup> Micro with USB in IP65

### General ordering data

Version	FrontCom Micro USB coupling, USB 2.0, Type A
Order No.	<a href="#">1018840000</a>
Type	IE-FCM-USB-A
GTIN (EAN)	4032248730094
Qty.	10 pc(s).

Creation date February 15, 2023 4:20:24 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

## IE-FCM-USB-A

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Wall thickness, min.	1 mm	Wall thickness, max.	3 mm
Net weight	17 g		

## Temperatures

Operating temperature	-40 °C...70 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	70 °C		

## General Info

Connection 1	USB A	Connection 2	USB A
Description of article	FrontCom Micro USB coupling, USB 2.0	Wiring	Type A
Colour	black	Housing main material	PA UL 94 V0
Type of mounting	Cabinet, Distribution box	Shielding	360° shield contact
Protection degree	IP65, in closed state	Plugging cycles	≥ 1500

## General standards

Certificate no. (cULus)	E316369	Connector standard	IEC 61076-3-107
-------------------------	---------	--------------------	-----------------

## Classifications

ETIM 6.0	EC001031	ETIM 7.0	EC001031
ETIM 8.0	EC001031	ECLASS 9.0	27-18-27-02
ECLASS 9.1	27-18-27-90	ECLASS 10.0	27-18-27-02
ECLASS 11.0	27-18-27-02	ECLASS 12.0	27-18-28-92

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E316369

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">DUXR.E316369</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a> <a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>


**IE-FCM-USB-A**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Dimensioned drawing**



**Installation cut-out**

