

PAP PDU6/10 BL**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Product image

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

General ordering data

| | |
|---------------------|--|
| Version | P-series, End plate, blue, 2.5 mm |
| Order No. | 104920000 |
| Type | PAP PDU6/10 BL |
| GTIN (EAN) | 4032248788330 |
| Qty. | 50 pc(s). |
| Delivery status | This article will no longer be available in the future. |
| Available until | 2023-03-31 |
| Alternative product | 199195000 |

PAP PDU6/10 BL

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Depth | 32.55 mm | Depth (inches) | 1.281 inch |
| Height | 62.94 mm | Height (inches) | 2.478 inch |
| Width | 2.5 mm | Width (inches) | 0.098 inch |
| Net weight | 3.38 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 120 °C | | |

Material data

| | | | |
|---------------------------|-------|--------|------|
| Material | Wemid | Colour | blue |
| UL 94 flammability rating | V-0 | | |

System specifications

| | |
|---------|-----------|
| Version | End plate |
|---------|-----------|

Additional technical data

| | | | |
|---------------------|-----------------|------------------|-----------------|
| Installation advice | Direct mounting | Type of mounting | Direct mounting |
|---------------------|-----------------|------------------|-----------------|

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000886 | ETIM 7.0 | EC000886 |
| ETIM 8.0 | EC000886 | ECLASS 9.1 | 27-14-11-33 |
| ECLASS 10.0 | 27-14-11-33 | ECLASS 11.0 | 27-14-11-33 |
| ECLASS 12.0 | 27-14-11-33 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S |
| User Documentation | StorageConditionsTerminalBlocks BPZL ZQV/PAP |
| Catalogues | Catalogues in PDF-format |