

**WQV 35/2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image****Power feed-in**

Our wide range of W-Series terminal blocks with our WPD main line branch terminals, which are optimised to guarantee both convenience and space gains, ensures a secure and convenient connection at the power feed-in.

**General ordering data**

Version	W-Series, Cross-connector, For the terminals, Number of poles: 2
Order No.	<a href="#">1053060000</a>
Type	WQV 35/2
GTIN (EAN)	4008 19009 7349
Qty.	50 pc(s).

## WQV 35/2

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	28 mm	Depth (inches)	1.102 inch
Height	28 mm	Height (inches)	1.102 inch
Width	9.85 mm	Width (inches)	0.388 inch
Net weight	13.02 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

### Material data

Material	PA 66	Colour	yellow
UL 94 flammability rating	V-0		

### System specifications

Version	For the terminals
---------	-------------------

### Additional technical data

Installation advice	Direct mounting	Type of fixing	when screwed in
---------------------	-----------------	----------------	-----------------

### Cross-connector

Number of cross-connected terminals	2	Rated current, 2-pole	125 A
Rated current, multi-pole	135 A	Tightening torque range for fixing screw	1.2...2.4 Nm
Type	Cross-connector		

### Dimensions

Pitch in mm (P)	16 mm	TS 35 offset	28 mm
-----------------	-------	--------------	-------

### General

Installation advice	Direct mounting	Number of poles	2
---------------------	-----------------	-----------------	---

### Rating data

Rated voltage	400	Rated current	138 A
---------------	-----	---------------	-------

### Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

**WQV 35/2**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Approvals**

Approvals



ROHS

Conform

**Downloads**

Approval/Certificate/Document of  
Conformity

[EAC certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[WSCAD, Zuken E3.S](#)

User Documentation

[Beipackzettel\\_WQV.pdf](#)  
[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures