

**THM MT30X 38/17 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

**General ordering data**

|                    |   |
|--------------------|---|
| Version            | THM, Device markers, 17 x 38 mm, white                |
| Order No.          | <a href="#">1011610000</a>                            |
| Type               | THM MT30X 38/17 WS                                    |
| GTIN (EAN)         | 4032248718870   |
| Qty.               | 1 pc(s).  |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a> |

Creation date May 4, 2023 4:56:34 PM CEST

Catalogue status 28.04.2023 / We reserve the right to make technical changes.

## THM MT30X 38/17 WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.08 mm | Depth (inches)  | 0.003 inch |
| Height     | 17 mm   | Height (inches) | 0.669 inch |
| Width      | 38 mm   | Width (inches)  | 1.496 inch |
| Net weight | 494 g   |                 |            |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

## General data

|                                   |                               |  |                             |
|-----------------------------------|-------------------------------|--|-----------------------------|
| Adhesive                          | Acrylate adhesive             | Approval acc. to UL 969                      | Yes                         |
| Colour                            | white                         | Halogen                                      | No                          |
| Material                          | Polyester                     | Material colour according to resistance code | 9                           |
| Number of markers per combination | 1 Label reel = Device markers | Number per roll                              | 4,000                       |
| Operating temperature range       | -40...150 °C                  | Operating temperature range, max.            | 150 °C                      |
| Operating temperature range, min. | -40 °C                        | Printing method                              | Thermal transfer            |
| UL 94 flammability rating         | V-0                           | Version                                      | Self-adhesive, halogen-free |
| Width                             | 38 mm                         |  |                             |

## Device markers

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ECLASS 9.0  | 27-40-06-29 |
| ECLASS 9.1  | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Engineering Data | <a href="#">WSCAD</a>                    |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

**Data sheet**

**THM MT30X 38/17 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

