

Q 20 WDL2.5S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image**Building installation wiring**

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

General ordering data

Version	W-Series, Cross-connector, For the terminals, Number of poles: 20
Order No.	1074200000
Type	Q 20 WDL2.5S
GTIN (EAN)	4008 1909 10501
Qty.	20 pc(s).

Creation date February 28, 2023 9:40:31 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

Q 20 WDL2.5S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	9.5 mm	Depth (inches)	0.374 inch
Height	119.9 mm	Height (inches)	4.72 inch
Width	4 mm	Width (inches)	0.157 inch
Net weight	15.55 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	tinned copper	Colour	yellow
----------	---------------	--------	--------

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Explosion-tested version	No	Installation advice	Feed-through (bushing), Direct mounting
Type of fixing	when screwed in		

Dimensions

Pitch in mm (P)	6.1 mm
-----------------	--------

General

Installation advice	Feed-through (bushing), Direct mounting	Number of poles	20
---------------------	--	-----------------	----

Rating data

Rated current	24 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	abe9d042-078a-4094-b143-0a6a4ced35a2

Q 20 WDL2.5S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Approvals**

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of
Conformity

[EAC certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[WSCAD, Zuken E3.S](#)

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures