

**WQL 3 WFF300****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Bolt-type screw terminals, Cross-connector, Number of poles: 3
Order No.	<a href="#">1065800000</a>
Type	WQL 3 WFF300
GTIN (EAN)	4008 19003 1312
Qty.	5 pc(s).

Creation date March 1, 2023 3:55:18 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## WQL 3 WFF300

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	5 mm	Depth (inches)	0.197 inch
Height	150 mm	Height (inches)	5.905 inch
Width	40 mm	Width (inches)	1.575 inch
Net weight	234.81 g		

## Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

## Material data

Material	Copper - zinc	Colour	grey
----------	---------------	--------	------

## Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

## Cross-connector

Number of cross-connected terminals	3	Rated current, 2-pole	520 A
Rated current, multi-pole	520 A	Type	Cross-connector

## Dimensions

Pitch in mm (P)	55 mm
-----------------	-------

## General

Installation advice	Direct mounting	Number of poles	3
---------------------	-----------------	-----------------	---

## Rating data

Rated current	520 A
---------------	-------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

## Approvals

Approvals



ROHS	Conform
------	---------

**WQL 3 WFF300**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

---

Approval/Certificate/Document of Conformity	<a href="#">EAC certificate</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

---