

HDC CM ST F

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Flexible and all-purpose – the proper solution for many applications

ConCept is a modular system consisting of modules and frames. Together, they form a complete insert that can easily be integrated into an HDC housing.

The patented modular system allows you to put together individual connector variants.

A variety of modules for power, signal and data transmission are supplemented further by modules intended for pneumatics, and SC/LC cables.

The sturdy, one-piece module-frame design (optionally available in polycarbonate or die-cast zinc) and the integrated module-release aid both improve handling of the product.

General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	1157980000
Type	HDC CM ST F
GTIN (EAN)	4032248945498
Qty.	1 pc(s).

HDC CM ST F

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	34 mm	Depth (inches)	1.339 inch
Height	47 mm	Height (inches)	1.85 inch
Width	22.8 mm	Width (inches)	0.898 inch
Net weight	12.96 g		

Temperatures

Limit temperature	-40 °C ... 70 °C
-------------------	------------------

ConCept Pneumatic module

Colour	beige	UL 94 flammability rating	V-0
--------	-------	---------------------------	-----

Dimensions

Height of socket	47 mm	Total length base	34 mm
Width	22.8 mm		

General data

Free from halogens	false	Insulation strength	$\leq 10^{10}$ m Ω
Low smoke acc. DIN EN 45545-2	Yes	Material	Polycarbonate
Rated current (DIN EN 61984)	1 A	Rated impulse voltage (DIN EN 61984)	1 kV
Rated voltage (DIN EN 61984)	50 V	Series	ConCept module
Type	Female	UL 94 flammability rating	V-0
Volume resistance	≤ 20 m Ω		

Version

Material	Polycarbonate	Volume resistance	≤ 20 m Ω
----------	---------------	-------------------	----------------------

Classifications

ETIM 6.0	EC002312	ETIM 7.0	EC002312
ETIM 8.0	EC002312	ECLASS 9.0	27-44-02-92
ECLASS 9.1	27-44-02-18	ECLASS 10.0	27-44-02-92
ECLASS 11.0	27-44-02-92	ECLASS 12.0	27-44-02-92

Environmental Product Compliance

REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	1609748e-c278-4c9b-b3d1-e6215d2988cd

Approvals

Approvals



ROHS	Conform
------	---------

HDC CM ST F

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Downloads**

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN