

**HTF HYB****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Crimping tools for Weidmüller contacts for RSV and DSTV-HD systems**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

**General ordering data**

Version	Pressing tool, Crimping tool for contacts, 0.08mm <sup>2</sup> , 1mm <sup>2</sup> , FoderBcrimp
Order No.	<a href="#">1119580000</a>
Type	HTF HYB
GTIN (EAN)	4032248900626
Qty.	1 pc(s).

Creation date March 7, 2023 4:20:00 PM CET

**HTF HYB**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	200 mm	Width (inches)	7.874 inch
Net weight	443.2 g		

**Technical data**

Description of article	(1)Crimping tool
------------------------	------------------

**Description of contact**

Crimping range, max.	1 mm <sup>2</sup>	Crimping range, min.	0.08 mm <sup>2</sup>
----------------------	-------------------	----------------------	----------------------

**tool data crimping**

Crimping profile 1, max.	0.2 mm <sup>2</sup>	Crimping profile 1, min.	0.08 mm <sup>2</sup>
Crimping profile 2, max.	0.5 mm <sup>2</sup>	Crimping profile 2, min.	0.2 mm <sup>2</sup>
Crimping profile 3, max.	1 mm <sup>2</sup>	Crimping profile 3, min.	0.75 mm <sup>2</sup>
Crimping type/profile	FoderBcrimp		

**Classifications**

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

**Approvals**

Approvals



**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**Data sheet**

**HTF HYB**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

