


TRANSCLINIC 8I+**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**String monitoring with Transclenic xi+
A system that permanently monitors the
performance of photovoltaic facilities.**

The Transclenic xi+ series continuously monitors the power from single strings or groups of strings as well as the voltage of a Photovoltaic system and thereby permits detailed monitoring of the system. Negative influences, which lead to reduced output, can be detected immediately allowing rapid repairs or adjustments to be made to the system.

General ordering data

Version	Photovoltaics, Current monitoring, 8-channel, 1000 V
Order No.	1238120000
Type	TRANSCLINIC 8I+
GTIN (EAN)	4050118044232
Qty.	1 pc(s).

Creation date March 7, 2023 7:05:50 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

TRANSCLINIC 8I+

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	92.2 mm	Height (inches)	3.63 inch
Width	109.5 mm	Width (inches)	4.311 inch
Length	295 mm	Length (inches)	11.614 inch
Net weight	1,112 g		

Temperatures

Continuous operating temp., min.	-20 °C	Continuous operating temp., max.	70 °C
----------------------------------	--------	----------------------------------	-------

Technical data

Communication	MODBUS RS485 RTU	Digital inputs	0,5 V low, 15 ... 24 V high
Height	≤ 3000 m	Maximum current per string	30 A DC (-25...+70 °C)
Maximum number of strings	8	Measurement range	3...30 A DC
Number of digital inputs	2	Power consumption	< 1500 mW
Rated voltage	1000 V DC	String-current measurement error	± 360 mA from 3 A DC to 30 A DC
String-voltage measurement error	± 10 V from 100 V DC to 1000 V DC	Voltage supply	19 - 36 V DC
current measuring	Low-current measurement resistors (shunt)		

Classifications

ETIM 6.0	EC002928	ETIM 7.0	EC002928
ETIM 8.0	EC002928	ECLASS 9.0	22-57-92-03
ECLASS 9.1	22-57-04-90	ECLASS 10.0	22-57-04-90
ECLASS 11.0	22-57-02-92	ECLASS 12.0	22-57-02-92

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	TRANSCLINIC 14I+
Engineering Data	CAD data – STEP
User Documentation	Manual TC8i+_14i+
Catalogues	Catalogues in PDF-format

TRANSCLINIC 8I+

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Drawings

www.weidmueller.com

