

**EBR-MODULE RS232****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image****Module for saving and loading a device configuration**

- Reduced system downtime by simple reconfiguration if equipment is swapped over
- Automatic loading of the saved configuration possible after device restart
- Compact and robust design
- Useable with all Weidmüller managed switches and industrial WLAN devices

**General ordering data**

Version	Configuration module, IP40, 0 °C...60 °C
Order No.	<a href="#">1241430000</a>
Type	EBR-MODULE RS232
GTIN (EAN)	4050118029086
Qty.	1 Stück

## EBR-MODULE RS232

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	97 mm	Depth (inches)	3.819 inch
Height	12 mm	Height (inches)	0.472 inch
Width	32.5 mm	Width (inches)	1.28 inch
Net weight	50 g		

### Temperatures

Storage temperature	-20 °C...70 °C	Operating temperature	0 °C...60 °C
Operating temperature, min.	0 °C	Operating temperature, max.	60 °C
Humidity	5 to 95 % (non-condensing)		

### EMC conformity and approvals

EMC standards	FCC Part 15, CISPR (EN55022) Class A, EN 61000-4-2 (ESD), Stage 2, EN 61000-4-3 (RS), Stage 3, EN 61000-4-4 (EFT), Stage 3, EN 61000-4-5 (surge voltage), Stage 3, EN 61000-4-6 (CS), Stage 3		
---------------	---	--	--

### Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	60 °C
Operating temperature, min.	0 °C	Storage temperature, max.	70 °C
Storage temperature, min.	-20 °C		

### Guarantee

Time interval	5 years
---------------	---------

### Power supply

Connection type	RJ45-Port, RS232
-----------------	------------------

### Technical data

Cable length	0.35 m	Housing main material	PVC casting
Protection degree	IP40	Type of fixing	M4 screw (< 4 mm)

### Classifications

ETIM 6.0	EC000734	ETIM 7.0	EC000734
ECLASS 9.0	19-17-92-90	ECLASS 9.1	19-17-01-25
ECLASS 10.0	19-17-92-90	ECLASS 11.0	19-17-90-90
ECLASS 12.0	19-17-90-90		

## EBR-MODULE RS232

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Approvals

Approvals



ROHS

Conform

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity</a> <a href="#">UK Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Hardware Installation Guide</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	