

KLBUE 10-20 CPF16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Product image



Similar to illustration

Thanks to special mounting feet, the product portfolio also includes shield clamping saddles that can be mounted on the C-profiles. The shield is diverted from the shield clamping saddles via the mounting foot to the C-profiles and thus to PE (ground).

General ordering data

Version	Clamping yoke, Clamping yoke for shield connection, Steel
Order No.	1252550000
Type	KLBUE 10-20 CPF16
GTIN (EAN)	4050118104431
Qty.	10 Stück

Erstellungs-Datum May 25, 2023 12:23:29 PM CEST

KLBUE 10-20 CPF16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	39.5 mm	Depth (inches)	1.555 inch
Height	26 mm	Height (inches)	1.024 inch
Width	25 mm	Width (inches)	0.984 inch
Mounting dimension - width	24 mm	Net weight	43.3 g

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Steel	Colour	grey
----------	-------	--------	------

System specifications

Rail	TS 27
------	-------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Snap-on	Type of mounting	Screw

Conductors for clamping (rated connection)

Cable diameter, max.	20 mm	Cable diameter, min.	10 mm
----------------------	-------	----------------------	-------

Dimensions

Pitch in mm (P)	25 mm
-----------------	-------

General

Installation advice	Direct mounting	Rail	TS 27
---------------------	-----------------	------	-------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50	ECLASS 12.0	27-14-11-50

Approvals

Approvals



ROHS	Conform
------	---------

KLBUE 10-20 CPF16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Downloads

Approval/Certificate/Document of Conformity	EAC certificate
Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
User Documentation	Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	