

**STB 36.8/IH/WS WTL6/1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The test socket is used to connect test devices with a standard 4.0 plug. Depending on the potential within the application, different colors of the test sockets can be selected for quick and easy maintenance work.

**General ordering data**

Version	Accessories, Socket
Order No.	<a href="#">1312560000</a>
Type	STB 36.8/IH/WS WTL6/1
GTIN (EAN)	4050118181203
Qty.	50 pc(s).
Delivery status	<b>This article will no longer be available in the future.</b>
Available until	2022-08-31
Alternative product	<a href="#">1936280000</a>

Creation date March 6, 2023 9:15:09 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## STB 36.8/IH/WS WTL6/1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	39.8 mm	Depth (inches)	1.567 inch
Height	36.8 mm	Height (inches)	1.449 inch
Width	6 mm	Width (inches)	0.236 inch
Diameter	6 mm	Net weight	4.98 g

## Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

## Material data

Material	Polyamide 66	Colour	white
UL 94 flammability rating	V-2		

## System specifications

Version	For the terminals
---------	-------------------

## Additional technical data

Installation advice	Direct mounting	Type of mounting	when screwed in
---------------------	-----------------	------------------	-----------------

## Dimensions

Diameter	6 mm	Plug-in depth	11.1 mm
----------	------	---------------	---------

## General

Installation advice	Direct mounting	Operating temperature range, max.	100 °C
---------------------	-----------------	-----------------------------------	--------

## Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	dce63e23-eea1-4eaa-9071-1c98fc8fa2ea

## Approvals

Approvals



ROHS	Conform
------	---------

**STB 36.8/IH/WS WTL6/1**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

---

Approval/Certificate/Document of Conformity	<a href="#">EAC certificate</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

---