

**KTB RNHD 624520 S4E R**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Similar to illustration**



Abbildung ähnlich

**Integrate, expand and customise: The ideal expansion for every application**

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

**Rain Covers**

The rain cover provides an ideal, additional level of protection for the enclosure if it is installed in unusual climatic zones with, for instance, very heavy rainfall or extreme levels of direct sunlight.

**General ordering data**

|            |   |
|------------|---|
| Version    | Klippon TB (Terminal Box), Rain hood, Height: 55.9 mm, Width: 455 mm, Depth: 211.2 mm, Material: Stainless steel 1.4404 (316L), electropolished, silver |
| Order No.  | <a href="#">1314280000</a>  |
| Type       | KTB RNHD 624520 S4E R   |
| GTIN (EAN) | 4050118117554   |
| Qty.       | 1 Stück   |

Erstellungs-Datum May 25, 2023 12:29:53 PM CEST

## KTB RNHD 624520 S4E R

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 211.2 mm | Depth (inches)  | 8.315 inch  |
| Height     | 55.9 mm  | Height (inches) | 2.201 inch  |
| Width      | 455 mm   | Width (inches)  | 17.913 inch |
| Net weight | 1,700 g  |                 |             |

### General information

|          |                               |                |                 |
|----------|-------------------------------|----------------|-----------------|
| Material | Stainless steel 1.4404 (316L) | Surface finish | electropolished |
|----------|-------------------------------|----------------|-----------------|

### General information on accessories

|          |                               |                |                 |
|----------|-------------------------------|----------------|-----------------|
| Material | Stainless steel 1.4404 (316L) | Surface finish | electropolished |
|----------|-------------------------------|----------------|-----------------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000744    | ETIM 7.0    | EC000744    |
| ETIM 8.0    | EC000744    | ECLASS 9.0  | 27-18-24-05 |
| ECLASS 9.1  | 27-18-92-90 | ECLASS 10.0 | 27-18-24-05 |
| ECLASS 11.0 | 27-18-24-05 | ECLASS 12.0 | 27-18-24-05 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |  |
|--------------------|--|
| Engineering Data   | <a href="#">EPLAN</a>                    |
| User Documentation | <a href="#">INSTR.KTB.RNHD.R</a>         |
| Catalogues         | <a href="#">Catalogues in PDF-format</a> |
| Brochures          |  |