

QVS 2/4 SAKT4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

QVS4 030740

Similar to illustration

The short current bridges are inserted into two instrument transformer wiring terminal blocks. By using the short-circuit bridge, the desired short-circuit could be realized within the application for maintenance work.

General ordering data

Version	SAK Series, Cross-connector, Cross-connector, Number of poles: 2
Order No.	1319260000
Type	QVS 2/4 SAKT4
GTIN (EAN)	4008 190136512
Qty.	20 pc(s).

Creation date March 6, 2023 5:35:16 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

QVS 2/4 SAKT4

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	10.5 mm	Depth (inches)	0.413 inch
Height	22.3 mm	Height (inches)	0.878 inch
Width	11 mm	Width (inches)	0.433 inch
Net weight	0.767 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Material data

Material	PA 66	Colour	orange
UL 94 flammability rating	V-2		

System specifications

Version	Cross-connector
---------	-----------------

Additional technical data

Explosion-tested version	No	Type of fixing	when screwed in
Type of mounting	when screwed in		

Dimensions

Pitch in mm (P)	12 mm	TS 35 offset	45.5 mm
-----------------	-------	--------------	---------

General

Number of poles	2	Operating temperature range, max.	100 °C
-----------------	---	-----------------------------------	--------

Rating data

Rated current	32 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

Approvals

Approvals



ROHS

Conform

Data sheet**QVS 2/4 SAKT4**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Downloads**

Approval/Certificate/Document of Conformity	EAC certificate
Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	
