


**SM 44/44-21 MC NE GR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|                    |   |
|--------------------|---|
| Version            | SwitchMark, Device markers, 44 x 44 mm, for cam switches, ABB, Type ON and OL40, grey |
| Order No.          | <a href="#">132360000</a>   |
| Type               | SM 44/44-21 MC NE GR  |
| GTIN (EAN)         | 4050118126914   |
| Qty.               | 20 Stück  |
| compatible printer | <a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a>      |

## SM 44/44-21 MC NE GR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|          |        |                 |            |
|----------|--------|-----------------|------------|
| Depth    | 1.2 mm | Depth (inches)  | 0.047 inch |
| Height   | 44 mm  | Height (inches) | 1.732 inch |
| Width    | 44 mm  | Width (inches)  | 1.732 inch |
| Diameter | 21 mm  | Net weight      | 3.56 g     |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

### General data

|  |   |                                   |                              |
|--|---|-----------------------------------|------------------------------|
| Application/manufacturere                    | for cam switches, ABB, Type ON and OL40 | Colour                            | grey                         |
| Halogen                                      | No                                      | Material                          | Polyamide 66                 |
| Material colour according to resistance code | 8                                       | Number of markers per combination | 1 MultiCard = Device markers |
| Operating temperature range                  | -40...100 °C                            | Operating temperature range, max. | 100 °C                       |
| Operating temperature range, min.            | -40 °C                                  | UL 94 flammability rating         | V-2                          |
| Width  | 44 mm                                   |                                   |                              |

### Device markers

|          |       |         |    |
|----------|-------|---------|----|
| Diameter | 21 mm | Halogen | No |
|----------|-------|---------|----|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ECLASS 9.0  | 27-40-06-29 |
| ECLASS 9.1  | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Engineering Data | <a href="#">WSCAD, EPLAN</a>             |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

**SM 44/44-21 MC NE GR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

