

**H1,0/16D R BD GSP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

- Linked wire-end ferrules on reel (5,000 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

**General ordering data**

Version	Wire-end ferrule, Standard, 12 mm, 10 mm, red
Order No.	<a href="#">1476090000</a>
Type	H1,0/16D R BD GSP
GTIN (EAN)	4050118282924
Qty.	5,000 pc(s).
Packaging	Reel

Creation date March 8, 2023 12:34:08 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

**H1,0/16D R BD GSP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 0.138 g

**Technical data**

Description of article	Wire-end ferrules on reel, red	Version	Standard
------------------------	--------------------------------	---------	----------

**Wire-end ferrules**

Collar diameter (D2)	3 mm	Colour code	DIN
Conductor cross-section	1 mm <sup>2</sup>	Contact surface diameter (D1)	1.4 mm
Contact surface length (L2)	10 mm	L1 in mm	16 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	12 mm	Wire connection cross section AWG, max.	AWG 17

**Classifications**

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E354986

**Downloads**

User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Data sheet**

**H1,0/16D R BD GSP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Drawing**

