

**KWN-M4/-1,5 90****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

**General ordering data**

Version	cable lug, terminal end, 1 mm <sup>2</sup> - 1.5 mm <sup>2</sup>
Order No.	<a href="#">1495220000</a>
Type	KWN-M4/-1,5 90
GTIN (EAN)	4050118304572
Qty.	100 Stück

Erstellungs-Datum May 16, 2023 12:39:19 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## KWN-M4/-1,5 90

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight 1.6 g

### Technical data

Version Euro series 90°

### Connectors

Conductor cross-section, max.	1.5 mm <sup>2</sup>	Conductor cross-section, min.	1 mm <sup>2</sup>
Connection length (l)	9 mm	Flange width (b)	8.5 mm
Hole	M 4	Inside diameter of flange (d2)	4.3 mm
Inside diameter of shaft (d1)	1.9 mm	Insulation	not available
Outside diameter of shaft (d3)	3.9 mm	Shaft length (a)	5 mm

### Classifications

ETIM 6.0	EC001051	ETIM 7.0	EC001051
ETIM 8.0	EC001051	ECLASS 9.0	27-40-02-05
ECLASS 9.1	27-40-02-05	ECLASS 10.0	27-40-02-05
ECLASS 11.0	27-40-02-05	ECLASS 12.0	27-40-02-05

### Approvals

ROHS Conform

### Downloads

Engineering Data [EPLAN](#)  
 Catalogues [Catalogues in PDF-format](#)  
 Brochures

**KWN-M4/-1,5 90**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Zeichnungen

