

KRN-M3/-1,5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

| | |
|------------|--|
| Version | cable lug, terminal end, 1 mm ² - 1.5 mm ² |
| Order No. | 1495040000 |
| Type | KRN-M3/-1,5 |
| GTIN (EAN) | 4050118304916 |
| Qty. | 100 Stück |

Erstellungs-Datum May 16, 2023 12:36:53 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

KRN-M3/-1,5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 1.2 g

Technical data

Version Euro series, standard

Connectors

| | | | |
|--------------------------------|---------------------|--------------------------------|-------------------|
| Conductor cross-section, max. | 1.5 mm ² | Conductor cross-section, min. | 1 mm ² |
| Connection length (l) | 14 mm | Flange width (b) | 6.5 mm |
| Hole | M 3 | Inside diameter of flange (d2) | 3.2 mm |
| Inside diameter of shaft (d1) | 1.9 mm | Insulation | not available |
| Outside diameter of shaft (d3) | 3.9 mm | Shaft length (a) | 6 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001051 | ETIM 7.0 | EC001051 |
| ETIM 8.0 | EC001051 | ECLASS 9.0 | 27-40-02-05 |
| ECLASS 9.1 | 27-40-02-05 | ECLASS 10.0 | 27-40-02-05 |
| ECLASS 11.0 | 27-40-02-05 | ECLASS 12.0 | 27-40-02-05 |

Approvals

ROHS Conform

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | EPLAN |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

KRN-M3/-1,5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

