

## KWN-M8/-25 90

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

### General ordering data

|            |  |
|------------|--|
| Version    | cable lug, terminal end,25 mm <sup>2</sup> |
| Order No.  | <a href="#">1495870000</a>                 |
| Type       | KWN-M8/-25 90                              |
| GTIN (EAN) | 4050118305470                              |
| Qty.       | 100 Stück                                  |

Erstellungs-Datum May 16, 2023 12:47:51 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## KWN-M8/-25 90

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight 14.06 g

### Technical data

Version Euro series 90°

### Connectors

|                                |                    |                                |         |
|--------------------------------|--------------------|--------------------------------|---------|
| Conductor cross-section        | 25 mm <sup>2</sup> | Connection length (l)          | 17.5 mm |
| Flange width (b)               | 16 mm              | Hole                           | M8      |
| Inside diameter of flange (d2) | 8.4 mm             | Inside diameter of shaft (d1)  | 7 mm    |
| Insulation                     | not available      | Outside diameter of shaft (d3) | 10 mm   |
| Shaft length (a)               | 14 mm              |                                |         |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001051    | ETIM 7.0    | EC001051    |
| ETIM 8.0    | EC001051    | ECLASS 9.0  | 27-40-02-05 |
| ECLASS 9.1  | 27-40-02-05 | ECLASS 10.0 | 27-40-02-05 |
| ECLASS 11.0 | 27-40-02-05 | ECLASS 12.0 | 27-40-02-05 |

### Approvals

Approvals



ROHS Conform

### Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">EPLAN</a>                    |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |
| Brochures        |  |

**KWN-M8/-25 90**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

