

KWN-M8/-10 90

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

| | |
|------------|---|
| Version | cable lug, terminal end, 10 mm ² |
| Order No. | 1497040000 |
| Type | KWN-M8/-10 90 |
| GTIN (EAN) | 4050118306576 |
| Qty. | 100 Stück |

Erstellungs-Datum May 16, 2023 1:02:01 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

KWN-M8/-10 90

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 6.71 g

Technical data

Version Euro series 90°

Connectors

| | | | |
|--------------------------------|--------------------|--------------------------------|---------|
| Conductor cross-section | 10 mm ² | Connection length (l) | 15.5 mm |
| Flange width (b) | 15 mm | Hole | M8 |
| Inside diameter of flange (d2) | 8.4 mm | Inside diameter of shaft (d1) | 4.5 mm |
| Insulation | not available | Outside diameter of shaft (d3) | 7 mm |
| Shaft length (a) | 9 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001051 | ETIM 7.0 | EC001051 |
| ETIM 8.0 | EC001051 | ECLASS 9.0 | 27-40-02-05 |
| ECLASS 9.1 | 27-40-02-05 | ECLASS 10.0 | 27-40-02-05 |
| ECLASS 11.0 | 27-40-02-05 | ECLASS 12.0 | 27-40-02-05 |

Approvals

Approvals



ROHS Conform

Downloads

| | |
|------------------|--|
| Engineering Data | EPLAN |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

KWN-M8/-10 90

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

