

KWPN-M10/-70 90**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

| | |
|------------|--|
| Version | cable lug, terminal end,70 mm ² |
| Order No. | 1497650000 |
| Type | KWPN-M10/-70 90 |
| GTIN (EAN) | 4050118307177 |
| Qty. | 25 Stück |

KWPN-M10/-70 90

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 65.1 g

Technical data

Version DIN series 46235, 90°

Connectors

| | | | |
|--------------------------------|--------------------|--------------------------------|---------|
| Conductor cross-section | 70 mm ² | Connection length (l) | 22.8 mm |
| Flange width (b) | 24 mm | Hole | M10 |
| Inside diameter of flange (d2) | 10.5 mm | Inside diameter of shaft (d1) | 11.3 mm |
| Insulation | not available | Outside diameter of shaft (d3) | 16.5 mm |
| Shaft length (a) | 28 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001050 | ETIM 7.0 | EC001050 |
| ETIM 8.0 | EC001050 | ECLASS 9.0 | 27-40-02-03 |
| ECLASS 9.1 | 27-40-02-03 | ECLASS 10.0 | 27-40-02-03 |
| ECLASS 11.0 | 27-40-02-03 | ECLASS 12.0 | 27-40-02-03 |

Approvals

ROHS Conform

Downloads

Engineering Data [EPLAN](#)
 Catalogues [Catalogues in PDF-format](#)

KWPN-M10/-70 90

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Zeichnungen

