

**KP-M6/-35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

**General ordering data**

|            |  |
|------------|--|
| Version    | cable lug, terminal end,35 mm <sup>2</sup> |
| Order No.  | <a href="#">1498020000</a>                 |
| Type       | KP-M6/-35                                  |
| GTIN (EAN) | 4050118307313                              |
| Qty.       | 100 Stück                                  |

## KP-M6/-35

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight 30.9 g

### Technical data

Version DIN series 46235,  
 standard

### Connectors

|                                |                    |                                |               |
|--------------------------------|--------------------|--------------------------------|---------------|
| Conductor cross-section        | 35 mm <sup>2</sup> | Connection length (l)          | 42.5 mm       |
| Flange width (b)               | 17.5 mm            | Hole                           | M 6           |
| Identification number Cu       | 12 K               | Inside diameter of flange (d2) | 6.4 mm        |
| Inside diameter of shaft (d1)  | 8.2 mm             | Insulation                     | not available |
| Outside diameter of shaft (d3) | 12.5 mm            | Shaft length (a)               | 20 mm         |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001050    | ETIM 7.0    | EC001050    |
| ETIM 8.0    | EC001050    | ECLASS 9.0  | 27-40-02-03 |
| ECLASS 9.1  | 27-40-02-03 | ECLASS 10.0 | 27-40-02-03 |
| ECLASS 11.0 | 27-40-02-03 | ECLASS 12.0 | 27-40-02-03 |

### Approvals

ROHS Conform

### Downloads

Engineering Data [EPLAN](#)  
 Catalogues [Catalogues in PDF-format](#)  
 Brochures

**KP-M6/-35**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

