

**ZQV 4N/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

**General ordering data**

Order No.	<a href="#">1527940000</a>
Type	ZQV 4N/3
GTIN (EAN)	4050118332865
Qty.	60 pc(s).

Creation date March 8, 2023 1:05:45 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

**ZQV 4N/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	27.95 mm	Depth (inches)	1.1 inch
Height	2.8 mm	Height (inches)	0.11 inch
Width	16 mm	Width (inches)	0.63 inch
Net weight	2.114 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Operating temperature	-60 °C...130 °C
Operating temperature, min.	-60 °C	Operating temperature, max.	130 °C
Continuous operating temp., min.	-60	Continuous operating temp., max.	130

**Material data**

Material	Wemid	Colour	orange
UL 94 flammability rating	V-0		

**Additional technical data**

Explosion-tested version	Yes	Type of fixing	Plugged
--------------------------	-----	----------------	---------

**Cross-connector**

Number of cross-connected terminals	3	Rated current, 2-pole	32 A
Rated current, multi-pole	32 A	Type	Cross-connector

**Dimensions**

Pitch in mm (P)	6.1 mm
-----------------	--------

**General**

Number of poles	3
-----------------	---

**Rating data**

Rated current	32 A
---------------	------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

**Important note**

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used
---------------------	---

## ZQV 4N/3

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

# Technical data

## Approvals

Approvals



ROHS

Conform

## Downloads

Approval/Certificate/Document of Conformity

- [EAC certificate](#)
- [DNVGL certificate](#)
- [BV certificate](#)
- [RINA certificate](#)
- [Lloyds Register Certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[WSCAD, Zuken E3.S](#)

User Documentation

- [2434520000\\_BED-ANL\\_ZQV\\_A\\_REIHE.pdf](#)
- [StorageConditionsTerminalBlocks](#)
- [BPZL ZQV 2.5](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures