

IE-FC-SET-SPDED001-KN-P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Version	FrontCom, Set
Order No.	1529580000
Type	IE-FC-SET-SPDED001-KN-P
GTIN (EAN)	4050118334432
Qty.	1 pc(s).
Reference product	1450510000 1450550000 1450730000 1019570000 1962840000

Creation date March 8, 2023 1:09:55 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

IE-FC-SET-SPDED001-KN-P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	134 mm	Depth (inches)	5.276 inch
Height	40 mm	Height (inches)	1.575 inch
Width	67 mm	Width (inches)	2.638 inch
Net weight	451 g		

General data

Material cover	Polycarbonate PC		
Material frame	Zinc diecast		
Product type	Set		
Protection degree	IP65, in closed state		
Reference product	Cardinality	1	
	Reference		IE-FC-SFP-KNOB
	Cardinality	1	
	Reference		IE-FC-SP-PWB/2ST
	Cardinality	1	
	Reference		IE-FCI-PWB-DE
	Cardinality	1	
	Reference		IE-BI-USB-A
	Cardinality	1	
	Reference		IE-BI-RJ45-C

Technical data

Data inserts	USB 2.0 A/A, RJ45 coupling Cat.6 _A	Frame	Plastic cover
Insert plate	2x data, 1x power, Shielded	Power inserts	Socket DE
Rated current for socket	16 A	Rated voltage for socket	250 V

General standards

Certificate No. (DNVGL)	TAA000022B
-------------------------	------------

Classifications

ETIM 6.0	EC001031	ETIM 7.0	EC001031
ETIM 8.0	EC001031	ECLASS 9.0	27-18-27-02
ECLASS 9.1	27-18-27-90	ECLASS 10.0	27-18-27-02
ECLASS 11.0	27-18-27-02	ECLASS 12.0	27-18-28-92

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	3767b26f-703a-492e-9234-36e83d1c0725

Approvals

Approvals



ROHS	Conform
------	---------

Creation date March 8, 2023 1:09:55 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

IE-FC-SET-SPDED001-KN-P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Downloads**Approval/Certificate/Document of
Conformity[GL_FrontCom](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[MAN IE GUIDE DE](#)[MAN IE GUIDE EN](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)[PI PROFINET CABLING EN](#)[PI PROFINET CABLING EN](#)

Data sheet

IE-FC-SET-SPDED001-KN-P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

