

IE-FCI-HD15-FF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Version	FrontCom, VGA coupling, Signal insert VGA/HD15, Socket / socket
Order No.	1556290000
Type	IE-FCI-HD15-FF
GTIN (EAN)	4050118369755
Qty.	1 pc(s).

Creation date March 8, 2023 1:41:23 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

IE-FCI-HD15-FF

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	9 g
------------	-----

Temperatures

Operating temperature	-55 °C...105 °C	Operating temperature, min.	-55 °C
Operating temperature, max.	105 °C		

General data

Insert type	Signal insert VGA/HD15	Product type	VGA coupling
Protection degree	IP20		

Electrical properties

Dielectric strength, contact / contact	1000 V _{eff} / 1 min	Insulation strength	1000 MΩ at 500 V DC
--	-------------------------------	---------------------	---------------------

General standards

Certificate No. (UR)	E497345
----------------------	---------

Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ECLASS 9.0	27-44-03-90
ECLASS 9.1	27-18-90-90	ECLASS 10.0	27-44-03-90
ECLASS 11.0	27-44-03-90	ECLASS 12.0	27-18-28-92

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	14f36bdb-8bcd-4f24-8fb3-9538ad1abec6

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E497345

Downloads

Approval/Certificate/Document of Conformity	GL_FrontCom
Engineering Data	CAD data – STEP
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	MB FREECONTACT EN FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

Creation date March 8, 2023 1:41:23 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.


IE-FCI-HD15-FF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings

Dimensioned drawing



Dimensioned drawing



Dimensioned drawing

