

**WKB 1/2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image****WKB 1/2 160428**

The short current bridges are inserted into two instrument transformer wiring terminal blocks. By using the short-circuit bridge, the desired short-circuit could be realized within the application for maintenance work.

**General ordering data**

Version	Accessories, Cross-connection slider, Cross-connector, Number of poles: 2
Order No.	<a href="#">1604280000</a>
Type	WKB 1/2
GTIN (EAN)	4008 190165338
Qty.	50 pc(s).

Creation date February 16, 2023 4:41:47 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

## WKB 1/2

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	6.1 mm	Depth (inches)	0.24 inch
Height	9.3 mm	Height (inches)	0.366 inch
Width	14.1 mm	Width (inches)	0.555 inch
Net weight	1.4 g		

## Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

## Material data

Material	Polyamide 66	Colour	orange
UL 94 flammability rating	V-2		

## System specifications

Version	Cross-connector
---------	-----------------

## Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in	Type of mounting	when screwed in

## Dimensions

Pitch in mm (P)	8 mm	TS 35 offset	47 mm
-----------------	------	--------------	-------

## General

Installation advice	Direct mounting	Number of poles	2
Operating temperature range, max.	100 °C		

## Rating data

Rated current	41 A
---------------	------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

## Approvals

Approvals



ROHS

Conform

**WKB 1/2****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Downloads**

---

Approval/Certificate/Document of Conformity	<a href="#">EAC certificate</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

---