

**ZQV 2.5/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

**General ordering data**

Version	Accessories, Cross-connector, 24 A
Order No.	<a href="#">1608870000</a>
Type	ZQV 2.5/3
GTIN (EAN)	4008 19006 1630
Qty.	60 pc(s).

Creation date February 15, 2023 4:48:21 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

**ZQV 2.5/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	27.6 mm	Depth (inches)	1.087 inch
Height	13.6 mm	Height (inches)	0.535 inch
Width	2.8 mm	Width (inches)	0.11 inch
Net weight	1.8 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60
Continuous operating temp., max.	130		

**Material data**

Material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

**System specifications**

Version	For the terminals
---------	-------------------

**Additional technical data**

Explosion-tested version	Yes	Installation advice	Direct mounting
Type of fixing	Plugged		

**Cross-connector**

Number of cross-connected terminals	3	Rated current, 2-pole	24 A
Rated current, multi-pole	24 A	Type	Cross-connector

**Dimensions**

Pitch in mm (P)	5.1 mm
-----------------	--------

**General**

Installation advice	Direct mounting	Number of poles	3
---------------------	-----------------	-----------------	---

**Rating data**

Rated current	24 A
---------------	------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

**Important note**

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used
---------------------	---

**ZQV 2.5/3**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Approvals**

Approvals



ROHS

Conform

**Downloads**

Approval/Certificate/Document of  
Conformity

[EAC certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[WSCAD, Zuken E3.S](#)

User Documentation

[Operating instructions\\_ZDU1.5-ZDU35\\_ZQV.pdf](#)  
[StorageConditionsTerminalBlocks](#)  
[BPZL ZQV 2.5](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures