

HDC-CR10-3S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The frames of the modular ConCept system allow ConCept modules to be attached. These frames are designed for sizes 3, 4, 6 and 8. Thus they can be fitted into corresponding enclosures of these sizes.

The fitting capacity of the frames ranges from 2 modules up to 7 modules. This allows the user to put together a custom connector assembly. .

The basic version consists of sturdy, one-piece modules frames available to the user in either polycarbonate or die-cast zinc

Frames are only compatible with each other when they are made of the same material and identical size.

General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept frame
Order No.	1682200000
Type	HDC-CR10-3S
GTIN (EAN)	4008 190473938
Qty.	5 pc(s).

Creation date March 1, 2023 10:50:47 AM CET

HDC-CR10-3S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	64 mm	Depth (inches)	2.52 inch
Height	35 mm	Height (inches)	1.378 inch
Width	34 mm	Width (inches)	1.339 inch
Net weight	43.6 g		

Temperatures

Operating temperature, min.	-40 °C	Operating temperature, max.	125 °C
-----------------------------	--------	-----------------------------	--------

ConCept Pneumatic module

Colour	black
--------	-------

Dimensions

Height of plug	35 mm	Total length base	64 mm
Width	34 mm		

General data

BG	4	Material	Polyamide, glass fibre-reinforced
Series	ConCept frame	Size	4
Type	Pin		

Connection data PE

Connection type PE	Screw connection	Tightening torque, max. PE connection	1.5 Nm
Tightening torque, min. PE connection	1.2 Nm		

Version

BG	4	Material	Polyamide, glass fibre-reinforced
Size	4		

Classifications

ETIM 6.0	EC002312	ETIM 7.0	EC002312
ETIM 8.0	EC002312	ECLASS 9.0	27-44-02-06
ECLASS 9.1	27-44-02-06	ECLASS 10.0	27-44-02-06
ECLASS 11.0	27-44-02-06	ECLASS 12.0	27-44-02-92

Approvals

Approvals



ROHS

Conform

Data sheet

HDC-CR10-3S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN
