

## SCT 4.6/520

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

Weidmüller stainless steel Series contains a comprehensive assortment of stainless steel cable ties for extreme conditions such as high temperatures or severe chemical effects.

- stainless steel AISI 316,
- ideal for use outdoors,
- radiation- and corrosion-resistant,
- anti-magnetic,
- no serrations, so no damage to the insulation.

### General ordering data

Version	Cable ties, 4.6 x 520 mm, Stainless steel 1.4301, 445 N
Order No.	<a href="#">1699920000</a>
Type	SCT 4.6/520
GTIN (EAN)	4008190892364
Qty.	100 Stück
Delivery status	<b>This article will no longer be available in the future.</b>
Available until	2022-12-31
Alternative product	<a href="#">2791420000</a>

Erstellungs-Datum May 30, 2023 2:34:37 PM CEST

## SCT 4.6/520

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

## Dimensions and weights

Depth	0.25 mm	Depth (inches)	0.01 inch
Height	520 mm	Height (inches)	20.472 inch
Width	4.6 mm	Width (inches)	0.181 inch
Net weight	4.9 g		

## Temperatures

Operating temperature range	-80...538 °C	Operating temperature, min.	-80 °C
Operating temperature, max.	538 °C		

## Installation materials

Cable diameter, max.	152 mm	For re-opening	No
Halogen	No	Material	Stainless steel 1.4301
Operating temperature range, max.	538 °C	Operating temperature range, min.	-80 °C
Tensile strength	445 N	Tensile strength (Pound-force)	100 lbf
UV-resistant	No		

## Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02

## Approvals

Approvals



ROHS

Conform

## Downloads

Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## SCT 4.6/520

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Zeichnungen

### Drawing

