

EA-RING MS/M 40**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | |
|------------|---|
| Version | EA (earthing rings), Earthing ring, Miscellaneous, M 40, Brass, nickel-plated |
| Order No. | 1736520000 |
| Type | EA-RING MS/M 40 |
| GTIN (EAN) | 4008 190963637 |
| Qty. | 10 Stück |

Erstellungs-Datum May 30, 2023 2:55:44 PM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

EA-RING MS/M 40

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Height | 86.5 mm | Height (inches) | 3.406 inch |
| Length | 86.5 mm | Length (inches) | 3.406 inch |
| Net weight | 21.1 g | | |

Certificate numbers cable gland

| | |
|----------------|----------------------------|
| Identification | Ex e II, II 2 GD, EEx d II |
|----------------|----------------------------|

General information

| | | | |
|---------------------------|----------------------|--------------------------|---------|
| Cable glands | M 40 | External thread | M 40 |
| Gap, internal dimension B | 44.5 mm | Inside diameter D2 | 13.5 mm |
| Material | Brass, nickel-plated | O.D. | 54 mm |
| Thickness | 1.5 mm | Width, outer dimension C | 30 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002317 | ETIM 7.0 | EC002317 |
| ETIM 8.0 | EC002317 | ECLASS 9.0 | 27-14-44-32 |
| ECLASS 9.1 | 27-14-44-90 | ECLASS 10.0 | 27-14-44-32 |
| ECLASS 11.0 | 27-14-44-32 | ECLASS 12.0 | 27-14-08-07 |

Environmental Product Compliance

| | |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | WSCAD, EPLAN |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

EA-RING MS/M 40

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

