

KLBUE 10-20 CPF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Thanks to special mounting feet, the product portfolio also includes shield clamping saddles that can be mounted on the C-profiles. The shield is diverted from the shield clamping saddles via the mounting foot to the C-profiles and thus to PE (ground).

General ordering data

Version	Clamping yoke, Clamping yoke, Steel
Order No.	1752701001
Type	KLBUE 10-20 CPF
GTIN (EAN)	4032248044436
Qty.	10 Stück

KLBUE 10-20 CPF

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	39.5 mm	Depth (inches)	1.555 inch
Height	26 mm	Height (inches)	1.024 inch
Width	24 mm	Width (inches)	0.945 inch
Mounting dimension - width	22.5 mm	Net weight	36.048 g

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Steel	Colour	grey
----------	-------	--------	------

System specifications

Version	For a shield connection	Rail	TS 27
---------	-------------------------	------	-------

Additional technical data

Explosion-tested version	Yes	Installation advice	Direct mounting, Busbar
Type of fixing	when screwed in		

Conductors for clamping (rated connection)

Cable diameter, max.	20 mm	Cable diameter, min.	10 mm
----------------------	-------	----------------------	-------

Dimensions

Pitch in mm (P)	30 mm
-----------------	-------

General

Installation advice	Direct mounting, Busbar	Rail	TS 27
---------------------	-------------------------	------	-------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50	ECLASS 12.0	27-14-11-50

Approvals

Approvals



ROHS	Conform
------	---------

KLBUE 10-20 CPF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Downloads

Approval/Certificate/Document of Conformity	EAC certificate
Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
User Documentation	Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	