

**ZQV 1.5N/R3.5/7 GE****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Product image**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Accessories, Cross-connector, 17.5 A
Order No.	<a href="#">1754260000</a>
Type	ZQV 1.5N/R3.5/7 GE
GTIN (EAN)	4032248109692
Qty.	20 pc(s).

**ZQV 1.5N/R3.5/7 GE****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	12.15 mm	Depth (inches)	0.478 inch
Height	23.6 mm	Height (inches)	0.929 inch
Width	2.4 mm	Width (inches)	0.094 inch
Net weight	1.55 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50
Continuous operating temp., max.	120		

**Material data**

Material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

**System specifications**

Version	For the terminals
---------	-------------------

**Additional technical data**

Explosion-tested version	Yes	Installation advice	Direct mounting
Type of fixing	Plugged		

**Cross-connector**

Number of cross-connected terminals	7	Rated current, multi-pole	17.5 A
Type	Cross-connector		

**Dimensions**

Pitch in mm (P)	3.5 mm
-----------------	--------

**General**

Installation advice	Direct mounting	Number of poles	7
---------------------	-----------------	-----------------	---

**Rating data**

Rated current	17.5 A
---------------	--------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

**Important note**

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used
---------------------	---

**ZQV 1.5N/R3.5/7 GE****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

ROHS

Conform

**Downloads**

Engineering Data

[CAD data – STEP](#)

Engineering Data

[WSCAD, Zuken E3.S](#)

User Documentation

[StorageConditionsTerminalBlocks  
BPZL ZQV 2.5](#)

Catalogues

[Catalogues in PDF-format](#)