

**KLBUE 3-8 CPF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Thanks to special mounting feet, the product portfolio also includes shield clamping saddles that can be mounted on the C-profiles. The shield is diverted from the shield clamping saddles via the mounting foot to the C-profiles and thus to PE (ground).

**General ordering data**

Version	Clamping yoke, Clamping yoke, Steel
Order No.	<a href="#">1752681001</a>
Type	KLBUE 3-8 CPF
GTIN (EAN)	4032248044399
Qty.	10 Stück

## KLBUE 3-8 CPF

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	26 mm	Depth (inches)	1.024 inch
Height	18 mm	Height (inches)	0.709 inch
Width	14.5 mm	Width (inches)	0.571 inch
Mounting dimension - width	13.5 mm	Net weight	16.3 g

### Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

### Material data

Material	Steel	Colour	grey
----------	-------	--------	------

### System specifications

Version	For a shield connection	Rail	TS 27
---------	-------------------------	------	-------

### Additional technical data

Explosion-tested version	Yes	Installation advice	Direct mounting, Busbar
Type of fixing	when screwed in		

### Conductors for clamping (rated connection)

Cable diameter, max.	8 mm	Cable diameter, min.	3 mm
----------------------	------	----------------------	------

### Dimensions

Pitch in mm (P)	14 mm
-----------------	-------

### General

Installation advice	Direct mounting, Busbar	Rail	TS 27
---------------------	-------------------------	------	-------

### Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50	ECLASS 12.0	27-14-11-50

### Approvals

Approvals



ROHS	Conform
------	---------

## KLBUE 3-8 CPF

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">EAC certificate</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, EPLAN</a>
User Documentation	<a href="#">Beipackzettel_KLBUE.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	