

## CLI M 2-6 SDR CD

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections.

Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm<sup>2</sup>
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

### General ordering data

|            |  |
|------------|--|
| Version    | CableLine, Conductor and cable markers, 10 - 317 mm, 6 x 11.4 mm, yellow |
| Order No.  | <a href="#">1871789999</a>   |
| Type       | CLI M 2-6 SDR CD   |
| GTIN (EAN) | 4032248486182  |
| Qty.       | 250 Stück  |

Erstellungs-Datum May 22, 2023 12:09:47 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## CLI M 2-6 SDR CD

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 3 mm    | Depth (inches)  | 0.118 inch |
| Height     | 6 mm    | Height (inches) | 0.236 inch |
| Width      | 11.4 mm | Width (inches)  | 0.449 inch |
| Net weight | 0.24 g  |                 |            |

### Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

### General data

|                                   |  |                                   |                            |
|-----------------------------------|--|-----------------------------------|----------------------------|
| Colour                            | yellow   | Colour of printing                | black                      |
| Halogen                           | Yes  | Material                          | PVC, soft, without Cadmium |
| Number of markers per combination | 1 Component part = Conductor and cable markers | Operating temperature range       | -30...80 °C                |
| Operating temperature range, max. | 80 °C  | Operating temperature range, min. | -30 °C                     |
| Printed characters                | To customer specification                      | Printing                          | Custom printing            |
| Printing method                   | Ink jet technology                             | Type of printing                  | To customer specification  |
| UL 94 flammability rating         | V-0  | Version                           | CD                         |
| Width                             | 11.4 mm  |                                   |                            |

### Conductor and cable markers

|                               |                    |                                  |                          |
|-------------------------------|--------------------|----------------------------------|--------------------------|
| Conductor O.D.                | 10 - 317 mm        | Conductor O.D., max.             | 317 mm                   |
| Conductor O.D., min.          | 10 mm              | Conductor cross-section, max.    | 500 mm <sup>2</sup>      |
| Conductor cross-section, min. | 16 mm <sup>2</sup> | Cross-section for connected wire | 16 - 500 mm <sup>2</sup> |
| Halogen                       | Yes                |                                  |                          |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                             |  |
|-----------------------------|--|
| Engineering Data            | <a href="#">WSCAD, EPLAN</a>   |
| Product Change Notification | <a href="#">PCN CableLine_DE</a><br><a href="#">PCN CableLine_EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                             |

**CLI M 2-6 SDR CD**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**



Similar to illustration