

IE-PS-V04P-2LC-SM-BP**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



PushPull plug-in connector set according to IEC
61076-3-106 ver.4 (IEC24702), plastic with LC insert

General ordering data

Version	FO connector, Variant 4, LC-Duplex single-mode, with kink prevention, IP67
Order No.	1963350000
Type	IE-PS-V04P-2LC-SM-BP
GTIN (EAN)	4032248651825
Qty.	10 Stück

IE-PS-V04P-2LC-SM-BP

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	126.3 mm	Depth (inches)	4.972 inch
Height	20.1 mm	Height (inches)	0.791 inch
Width	20.2 mm	Width (inches)	0.795 inch
Net weight	43.1 g		

Temperatures

Operating temperature	-40 °C...70 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	70 °C		

General data

Colour	Miscellaneous	Connection 1	LC
Connection 2		Description of article	Variant 4, LC-Duplex single-mode, with kink prevention
	gluing, crimping, polishing	Housing main material	PA UL 94 V0
Fibre type	Singlemode	Insertion loss	0.5 dB singlemode, 0.4 dB multimode
Housing material, insert	PBT, Zinc diecast	Protection degree	IP67
Plugging cycles	500	Sheath diameter, max.	10 mm
Return loss (attenuation)	40 dB singlemode; 30 dB multimode		
Sheath diameter, min.	5 mm		

General standards

Connector standard	IEC 61076-3-106 Var. 4, IEC 61754-20
--------------------	--------------------------------------

Classifications

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22	ECLASS 12.0	19-17-01-22

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	e3782e8e-7b94-417d-a6f7-ac548c86df93

Approvals

Approvals



ROHS Conform

IE-PS-V04P-2LC-SM-BP

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Downloads

Approval/Certificate/Document of
Conformity

[GOST Approval](#)

Engineering Data

[WSCAD](#)

Product Change Notification

[20210412 Technical change for cap nut V1 and V4](#)
[20210412 Technische Änderung zu Hutmutter V1 und V4](#)

User Documentation

[MAN IE GUIDE DE](#)
[MAN IE GUIDE EN](#)
[Designation key / Type key](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)
[PI PROFINET CABLING EN](#)
[PI PROFINET CABLING EN](#)

IE-PS-V04P-2LC-SM-BP

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Zeichnungen

Dimensioned drawing

