

IE-PS-ST-MM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



FO ST plug-in connectors according to IEC 61754-2 for wire outer diameters 2.6 to 3 mm

General ordering data

Version	FO connector, Plug ST, multimode, IP20
Order No.	1968 150000
Type	IE-PS-ST-MM
GTIN (EAN)	4032248667147
Qty.	1 Stück

Erstellungs-Datum May 25, 2023 1:10:06 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

IE-PS-ST-MM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	47 mm	Depth (inches)	1.85 inch
Height	9.6 mm	Height (inches)	0.378 inch
Width	9.6 mm	Width (inches)	0.378 inch
Net weight	5 g		

Temperatures

Storage temperature	-40 °C...90 °C	Operating temperature	-20 °C...80 °C
Operating temperature, min.	-20 °C	Operating temperature, max.	80 °C

General data

Bending protection sleeve material	TPE	Cable pull-out force, min.	100 N
Colour	Miscellaneous	Connection 1	ST
Connection 2	gluing, crimping, polishing	Crimp barrel material	Copper, nickel-plated
Description of article	Plug ST, multimode	Dust protection cap material	TPE
Ferrule material	Zirconia	Fibre type	GOF, Multimode
Housing main material	Zinc diecast	Insertion loss	≤ 0.4 dB
Plugging cycles	1000	Protection degree	IP20
Return loss (attenuation)	≥ 30 dB	Sheath diameter, max.	3.2 mm
Sheath diameter, min.	2.6 mm		

General standards

Connector standard	IEC 61754-2
--------------------	-------------

Classifications

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22	ECLASS 12.0	19-17-01-22

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9229992a-00b9-4096-8962-200a7f33e289

Approvals

Approvals



ROHS Conform

IE-PS-ST-MM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Downloads

Approval/Certificate/Document of Conformity	GOST Approval
Engineering Data	WSCAD
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-PS-ST-MM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Zeichnungen

www.weidmueller.com

Dimensioned drawing

