

**SM 27/18 MM SW**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



**Prevention of incorrect operation: SM**

MultiMark device markers can be used with marking materials from different manufacturers. Wherever they are used, they ensure that all components, such as control and signalling devices from different vendors, are clearly assigned.

**Your benefits with MultiMark**

- “Different materials for various requirements”
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

**General ordering data**

|                    |   |
|--------------------|---|
| Version            | SwitchMark, Device markers, 18 x 27 mm, black         |
| Order No.          | <a href="#">2006320000</a>                            |
| Type               | SM 27/18 MM SW  |
| GTIN (EAN)         | 4050118390988   |
| Qty.               | 1,000 Stück   |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a> |

## SM 27/18 MM SW

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.1 mm  | Depth (inches)  | 0.004 inch |
| Height     | 18 mm   | Height (inches) | 0.709 inch |
| Width      | 27 mm   | Width (inches)  | 1.063 inch |
| Net weight | 0.153 g |                 |            |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...120 °C |
|-----------------------------|--------------|

### General data

|                                   |                             |                                   |        |
|-----------------------------------|-----------------------------|-----------------------------------|--------|
| Adhesive                          | Acrylate adhesive           | Approval acc. to UL 969           | Yes    |
| Colour                            | black                       | Halogen                           | No     |
| Material                          | Polyester                   | Number per roll                   | 1,000  |
| Operating temperature range       | -40...120 °C                | Operating temperature range, max. | 120 °C |
| Operating temperature range, min. | -40 °C                      | UL 94 flammability rating         | V-0    |
| Version                           | halogen-free, Self-adhesive | Width                             | 27 mm  |

### Device markers

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ECLASS 9.0  | 27-40-06-29 |
| ECLASS 9.1  | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Engineering Data | <a href="#">WSCAD, EPLAN</a>             |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

**Datenblatt**

**SM 27/18 MM SW**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

