

ELS 6/30 MM WS**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**ELS**

ELS tags are special and non-adhesive insertable labels for WKM cable markers or for group tag carriers. The matt, thin but tear-resistant polyester provides very good labelling and excellent readability. Used in combination with water-repellent WKM sleeves, the solution guarantees particularly long-lasting identification of cables even in harsh environments.

General ordering data

| | |
|--------------------|---|
| Version | ELS, Insert markers, 30 x 6 mm, white |
| Order No. | 2009980000 |
| Type | ELS 6/30 MM WS |
| GTIN (EAN) | 4050118396850 |
| Qty. | 3,000 Stück |
| compatible printer | 2599430000 2599440000 |

ELS 6/30 MM WS

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.14 mm | Depth (inches) | 0.006 inch |
| Height | 30 mm | Height (inches) | 1.181 inch |
| Width | 6 mm | Width (inches) | 0.236 inch |
| Net weight | 0.058 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|--------------|-----------------------------------|--------|
| Colour | white | Halogen | No |
| Material | Polyester | Number per roll | 3,000 |
| Operating temperature range | -40...150 °C | Operating temperature range, max. | 150 °C |
| Operating temperature range, min. | -40 °C | UL 94 flammability rating | HB |
| Version | halogen-free | Width | 6 mm |

Conductor and cable markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S, EPLAN |
| Catalogues | Catalogues in PDF-format |

ELS 6/30 MM WS

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Zeichnungen

