

## KTB GP 221513 CD S4 PE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Similar to illustration



Abbildung ähnlich

### **Integrate, expand and customise: The ideal expansion for every application**

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

#### **Flange plates**

Flange plates in two thicknesses, for easy replacement of pre-assembl

### General ordering data

|            |   |
|------------|---|
| Version    | Klippon TB (Terminal Box), flange plate, straight, Height: 177 mm, Width: 100 mm, Depth: 3 mm, Gland plates: left, right, Material: Stainless steel 1.4404, electropolished, silver |
| Order No.  | <a href="#">2022900000</a>  |
| Type       | KTB GP 221513 CD S4 PE  |
| GTIN (EAN) | 4050118403510   |
| Qty.       | 1 Stück   |

Erstellungs-Datum May 25, 2023 1:16:02 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## KTB GP 221513 CD S4 PE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 3 mm   | Depth (inches)  | 0.118 inch |
| Height     | 177 mm | Height (inches) | 6.968 inch |
| Width      | 100 mm | Width (inches)  | 3.937 inch |
| Net weight | 420 g  |                 |            |

### General information

|                    |                 |                       |                          |
|--------------------|-----------------|-----------------------|--------------------------|
| Gland plates       | left, right     | Material              | Stainless steel 1.4404   |
| Material thickness | 3 mm            | Protection class (UL) | Type 3, Type 4X, Type 12 |
| Surface finish     | electropolished |                       |                          |

### General information on accessories

|                |                        |                    |      |
|----------------|------------------------|--------------------|------|
| Material       | Stainless steel 1.4404 | Material thickness | 3 mm |
| Surface finish | electropolished        |                    |      |

### Housing earth

|                       |         |
|-----------------------|---------|
| Flange plate earthing | M6 x 15 |
|-----------------------|---------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000211    | ETIM 7.0    | EC000211    |
| ETIM 8.0    | EC000211    | ECLASS 9.0  | 27-14-24-21 |
| ECLASS 9.1  | 27-18-92-90 | ECLASS 10.0 | 27-14-24-21 |
| ECLASS 11.0 | 27-14-24-21 | ECLASS 12.0 | 27-14-24-21 |

### Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Engineering Data | <a href="#">EPLAN</a>                    |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |
| Brochures        |  |