

EPG 60**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 1.5 Ah

General ordering data

Version	Pressing tools, Tools, Pressing tool, 6mm ² , 300mm ² , Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping
Order No.	2453810000
Type	EPG 60
GTIN (EAN)	4050118468434
Qty.	1 pc(s).

Creation date March 9, 2023 8:57:12 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

EPG 60

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	355 mm	Height (inches)	13.976 inch
Width	100 mm	Width (inches)	3.937 inch
Net weight	6.5 g		

Technical data

Charging time	0.5 h		
Description of article	Crimping tool 6 - 300 mm ²		
Operating voltage	18 V DC		
Pressing force	nominal	60 kN	

Description of contact

Crimping range, max.	300 mm ²	Crimping range, min.	6 mm ²
----------------------	---------------------	----------------------	-------------------

tool data crimping

Crimping type/profile	Hexagonal crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping	Deviation	17 mm
Drive	Electro-hydraulic	Wire end ferrules cross-section, max.	300 mm ²
Wire end ferrules cross-section, min.	6 mm ²		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Approvals

Approvals



ROHS Conform

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format

Data sheet

EPG 60

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

