

**CMA-812-15-5A-7.5VA-0.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Cable-type current transformer**

The cable-type current transformer is mainly used for retrofitting in order to avoid cutting the primary conductors.

Due to its dimensions and the convenient handling, the cable-type current transformer is particularly suitable for use in places that are difficult to access or where space is limited.

The "click" system in conjunction with the fixing clamps even makes "one-handed" installation possible.

**General ordering data**

Version	Primary current: 1500 A, Secondary current max.: 5 A, Load: 7.5 VA, Tolerance class: 0,5, Split-core current transformer
Order No.	<a href="#">2438480000</a>
Type	CMA-812-15-5A-7.5VA-0.5
GTIN (EAN)	4050118450842
Qty.	1 Stück

Erstellungs-Datum June 2, 2023 9:50:00 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

**CMA-812-15-5A-7.5VA-0.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	58 mm	Depth (inches)	2.283 inch
Height	198 mm	Height (inches)	7.795 inch
Width	155 mm	Width (inches)	6.102 inch
Net weight	998 g		

### Temperatures

Storage temperature	-25 °C...40 °C	Operating temperature	-5 °C...40 °C
Operating temperature, min.	-5 °C	Operating temperature, max.	40 °C

### Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	80 mm
Rail	80 x 120 mm	Installation location	Indoor use

### Electrical attributes

Load	7.5 VA	Primary current	1,500 A
Secondary current max.	5 A	Tolerance class	0,5

### Classifications

ETIM 6.0	EC002048	ETIM 7.0	EC002048
ETIM 8.0	EC002048	ECLASS 9.0	27-21-09-02
ECLASS 9.1	27-21-09-02	ECLASS 10.0	27-21-09-02
ECLASS 11.0	27-21-09-02	ECLASS 12.0	27-21-09-02

### Approvals

ROHS	Conform
------	---------

### Downloads

User Documentation	<a href="#">Betriebsanleitung deutsch</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## CMA-812-15-5A-7.5VA-0.5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Zeichnungen

### Dimensional drawing

