

**HDC MHP200 M 50****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

**General ordering data**

|            |                                 |
|------------|---------------------------------|
| Version    | Pin, silver, 50 mm <sup>2</sup> |
| Order No.  | <a href="#">2514880000</a>      |
| Type       | HDC MHP200 M 50                 |
| GTIN (EAN) | 4050118528527                   |
| Qty.       | 10 Stück                        |

## HDC MHP200 M 50

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight 37.5 g

### Temperatures

Limit temperature -40 °C ... 125 °C

### General data

|                                    |                    |                                  |                    |
|------------------------------------|--------------------|----------------------------------|--------------------|
| Conductor cross-section, max.      | 50 mm <sup>2</sup> | Cross-section for connected wire | 50 mm <sup>2</sup> |
| Material                           | Copper alloy       | Production methods               | turned             |
| Stripping length, rated connection | 19 mm              | Surface finish                   | silver             |
| Type                               | Pin                | Type of connection               | Crimp connection   |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000796    | ETIM 7.0    | EC000796    |
| ETIM 8.0    | EC000796    | ECLASS 9.0  | 27-44-02-04 |
| ECLASS 9.1  | 27-44-02-04 | ECLASS 10.0 | 27-44-02-04 |
| ECLASS 11.0 | 27-44-02-04 | ECLASS 12.0 | 27-44-02-04 |

### Environmental Product Compliance

|            |                                      |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1                       |
| SCIP       | 6eabd5ae-2d6b-409e-8bdf-87c27ee10e40 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Engineering Data | <a href="#">EPLAN</a>                    |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

**HDC MHP200 M 50**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Zeichnungen**

[www.weidmueller.com](http://www.weidmueller.com)

