

SAIB-M-5S-IDC-M12-L-COD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Version	Field attachable connector, M12 socket
Order No.	2530760000
Type	SAIB-M-5S-IDC-M12-L-COD
GTIN (EAN)	4050118540581
Qty.	1 Stück

Erstellungs-Datum May 25, 2023 2:36:15 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

SAIB-M-5S-IDC-M12-L-COD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 49 g

Technical data customisable plug-in connectors

Cable diameter	5.8... 13.5 mm	Cable diameter, max.	13.5 mm
Cable diameter, min.	5.8 mm	Coding	L
Conductor cross-section, max.	1.5 mm ²	Conductor cross-section, min.	0.75 mm ²
Contact surface	Au (Gold)	Housing main material	Zinc diecast
Number of poles	5	Plugging cycles	500
Pollution severity	3	Protection degree	IP67, when screwed in
Rated current	12 A	Rated current	12 A
Rated voltage	63 V	Shield connection	Yes
Temperature range of housing	-40 ... +85 °C	Type of connection	Insulation displacement connection (IDC)

General Info

Number of poles	5	Connection 1	M12
Connection 2	IDC	Housing main material	Zinc diecast
Connection thread	M12 socket	Contact material	Cu
Contact surface	Au (Gold)	Protection degree	IP67, when screwed in
Plugging cycles	500		

Standards

Connector standard IEC 61076-2-111

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ECLASS 9.0	27-44-01-02
ECLASS 9.1	27-44-01-03	ECLASS 10.0	27-44-01-02
ECLASS 11.0	27-44-01-02	ECLASS 12.0	27-44-01-16

Environmental Product Compliance

REACH SVHC Lead 7439-92-1
 SCIP ebf89fc8-a87f-4691-b87a-dfb9921774b4

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data [CAD data – STEP](#)
 Catalogues [Catalogues in PDF-format](#)

SAIB-M-5S-IDC-M12-L-COD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Zeichnungen

www.weidmueller.com

Dimensioned drawing

